


Telescopic Slide Universal, 2 U

Universal Telescopic Slide with > 100 % extension and up to 61 kg load capacity.



CERTIFICATIONS



CARACTERISTICAS

Rail width k = 16 mm, max. installation width of extension/drawer w = 417 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing of the extension/drawer)

Locking at full extension

Extension length > 100 %

Static load-carrying capacity per pair 46 - 61 kg

ESPECIFICAÇÕES

Material:	Aço
Product Type:	Telescopic Slide
Acabamento:	Chapa de Aço Zincada

Table 1/1

Número de catálogo	Length	Quantidade por embalagem	Static Load	Tipo	Envio rápido
20110-100	305mm	2	61kg	Universal	Não

Número de catálogo	Length	Quantidade por embalagem	Static Load	Tipo	Envio rápido
20110-101	356mm	2	60kg	Universal	Não
20110-102	406mm	2	58kg	Universal	Não
20110-105	559mm	2	52kg	Universal	Não
20110-103	457mm	2	57kg	Universal	Não
20110-104	508mm	2	55kg	Universal	Não
20110-106	610mm	2	50kg	Universal	Não
20110-107	660mm	2	48kg	Universal	Não
20110-108	711mm	2	46kg	Universal	Não

DETALHES ADICIONAIS DO PRODUTO

To mount on 19" plane please order assembly kit separately Universal telescopic Rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE