


VMEbus J1/J2 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

CERTIFICATIONS



CARACTERÍSTICAS

In accordance with ANSI/VITA 1-1994 VME64 standard

Monolithic backplane, 6 U with J1 and J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination active/passive, switchable via jumpers; passive termination preset

Electronic automatic daisy chain (EDC)

Supply voltages provided via power bugs (ring tag M4) or FASTON

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-063	Backplane	3	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-064	Backplane	4	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-065	Backplane	5	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-066	Backplane	6	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-067	Backplane	7	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-068	Backplane	8	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-069	Backplane	9	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-070	Backplane	10	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-072	Backplane	12	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-080	Backplane	20	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-081	Backplane	21	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP

Table 2/3

Número de catálogo	Connector Type	Power Connector Type	Utility Connector Type	Altura	Largura	Quantidade por embalagem
23001-063	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	59.5mm	1
23001-064	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	79.8mm	1
23001-065	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	100.2mm	1
23001-066	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	120.5mm	1
23001-067	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	140.8mm	1

Número de catálogo	ConnectorType	Power ConnectorType	Utility ConnectorType	Altura	Largura	Quantidade por embalagem
23001-068	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	161.1mm	1
23001-069	DIN 41612, C96	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin, 5-pin Header	263.4mm	181.4mm	1
23001-070	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	201.8mm	1
23001-072	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	242.4mm	1
23001-080	DIN 41612, C96	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin, 5-pin Header	263.4mm	405mm	1
23001-081	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	425.3mm	1

Table 3/3

Número de catálogo	Envio rápido
23001-063	Não
23001-064	Não
23001-065	Não
23001-066	Não
23001-067	Não
23001-068	Não
23001-069	Não
23001-070	Não
23001-072	Não
23001-080	Não

Número de catálogo	Envio rápido
23001-081	Não

DETALHES ADICIONAIS DO PRODUTO

Other configurations available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE