

Secure Dual W-Lock Power Cord

Data Solutions



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

CARACTERÍSTICAS

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Tipo | Works With | Length | Cor | Altura | Input Cable Length |
|--------------------|-------|------------|--------|-------|--------|--------------------|
| EP1314024X150 | Cable | RackPower | 600mm | Black | 270mm | 588m |
| EP1314048X125 | Cable | RackPower | 1200mm | Black | 270mm | 1.176m |
| EP1314072X100 | Cable | RackPower | 1800mm | Black | 270mm | 1.764m |
| EP1314B24X150 | Cable | RackPower | 600mm | Blue | 270mm | 0.588m |
| EP1314B48X125 | Cable | RackPower | 1200mm | Blue | 270mm | 1.176m |

| Número de catálogo | Tipo | Works With | Length | Cor | Altura | Input Cable Length |
|--------------------|-------|------------|--------|----------|--------|--------------------|
| EP1314B72X100 | Cable | RackPower | 1800mm | Blue | 270mm | 1.764m |
| EP1314R24X150 | Cable | RackPower | 600mm | Vermelho | 270mm | 0.588m |
| EP1314R48X125 | Cable | RackPower | 1200mm | Vermelho | 270mm | 1.176m |
| EP1314R72X100 | Cable | RackPower | 1800mm | Vermelho | 270mm | 1.764m |
| EP1920024X100 | Cable | RackPower | 600mm | Black | 270mm | 0.588m |
| EP1920048X75 | Cable | RackPower | 1200mm | Black | 270mm | 1.176m |
| EP1920072X50 | Cable | RackPower | 1800mm | Black | 270mm | 1.764m |
| EP1920B24X100 | Cable | RackPower | 600mm | Blue | 270mm | 0.588m |
| EP1920B48X75 | Cable | RackPower | 1200mm | Blue | 270mm | 1.176m |
| EP1920B72X50 | Cable | RackPower | 1800mm | Blue | 270mm | 1.764m |
| EP1920R24X100 | Cable | RackPower | 600mm | Vermelho | 270mm | 0.588m |
| EP1920R48X75 | Cable | RackPower | 1200mm | Vermelho | 270mm | 1.176m |
| EP1920R72X50 | Cable | RackPower | 1800mm | Vermelho | 270mm | 1.764m |

Table 2/2

| Número de catálogo | Quantidade por embalagem | Plug Type | Removable Input Cable |
|--------------------|--------------------------|-----------|-----------------------|
| EP1314024X150 | 150 | C13/C14 | Não |

| Número de catálogo | Quantidade por embalagem | Plug Type | Removable Input Cable |
|--------------------|--------------------------|-----------|-----------------------|
| EP1314048X125 | 125 | C13/C14 | Não |
| EP1314072X100 | 100 | C13/C14 | Não |
| EP1314B24X150 | 150 | C13/C14 | Não |
| EP1314B48X125 | 125 | C13/C14 | Não |
| EP1314B72X100 | 100 | C13/C14 | Não |
| EP1314R24X150 | 150 | C13/C14 | Não |
| EP1314R48X125 | 125 | C13/C14 | Não |
| EP1314R72X100 | 100 | C13/C14 | Não |
| EP1920024X100 | 100 | C19/C20 | Não |
| EP1920048X75 | 75 | C19/C20 | Não |
| EP1920072X50 | 50 | C19/C20 | Não |
| EP1920B24X100 | 100 | C19/C20 | Não |
| EP1920B48X75 | 75 | C19/C20 | Não |
| EP1920B72X50 | 50 | C19/C20 | Não |
| EP1920R24X100 | 100 | C19/C20 | Não |
| EP1920R48X75 | 75 | C19/C20 | Não |
| EP1920R72X50 | 50 | C19/C20 | Não |

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos

representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE