

Varistar Colocation Cabinet, RAL 7035

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 7035 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



CARACTERÍSTICAS

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 7035

ESPECIFICAÇÕES

Product Type: Rack

Frame Material: Aço

Table 1/3

Número de catálogo	Rack Height	Altura	Cladding Material	Frame Color	Largura	Frame Color Code
--------------------	-------------	--------	-------------------	-------------	---------	------------------

11130-202	40U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-203	39U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-204	40U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-205	40U	2000mm	Aço	Light Grey	800mm	RAL 7021
11130-206	39U	2000mm	Aço	Light Grey	800mm	RAL 7035
11130-207	40U	2000mm	Aço	Light Grey	800mm	RAL 7021
11130-208	44U	2200mm	Aço	Light Grey	600mm	RAL 7021
11130-209	45U	2200mm	Aço	Light Grey	600mm	RAL 7021
11130-210	44U	2200mm	Aço	Light Grey	600mm	RAL 7021
11130-211	44U	2200mm	Aço	Light Grey	800mm	RAL 7021
11130-212	45U	2200mm	Aço	Black Grey	800mm	RAL 7021
11130-213	44U	2200mm	Aço	Light Grey	800mm	RAL 7021
11130-214	40U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-215	39U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-216	40U	2000mm	Aço	Light Grey	600mm	RAL 7021
11130-217	40U	2000mm	Aço	Light Grey	800mm	RAL 7021
11130-218	39U	2000mm	Aço	Black Grey	800mm	RAL 7021
11130-219	40U	2000mm	Aço	Light Grey	800mm	RAL 7021
11130-220	44U	2200mm	Aço	Light Grey	600mm	RAL 7021

11130-221	45U	2200mm	Aço	Light Grey	600mm	RAL 7021
11130-222	44U	2200mm	Aço	Light Grey	600mm	RAL 7021
11130-223	44U	2200mm	Aço	Light Grey	800mm	RAL 7021
11130-224	45U	2200mm	Aço	Light Grey	800mm	RAL 7021
11130-225	44U	2200mm	Aço	Light Grey	800mm	RAL 7021
11130-257	45U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-258	48U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-259	48U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-260	45U	2450mm	Aço	Light Grey	800mm	RAL 7021
11130-261	48U	2450mm	Aço	Light Grey	800mm	RAL 7021
11130-262	48U	2450mm	Aço	Light Grey	800mm	RAL 7021
11130-269	45U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-270	48U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-271	48U	2450mm	Aço	Light Grey	600mm	RAL 7021
11130-272	45U	2450mm	Aço	Light Grey	800mm	RAL 7021
11130-273	48U	2450mm	Aço	Light Grey	800mm	RAL 7021
11130-274	48U	2450mm	Aço	Light Grey	800mm	RAL 7021

Table 2/3

Número de catálogo	Cladding Color	Cladding Color Code	Profundidade	Quantidade por embalagem	Number of Compartments	Acabamento
--------------------	----------------	---------------------	--------------	--------------------------	------------------------	------------

11130-202	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-203	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-204	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado
11130-205	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-206	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-207	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado
11130-208	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-209	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-210	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado

11130-211	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-212	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-213	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado
11130-214	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-215	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-216	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado
11130-217	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-218	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-219	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado

11130-220	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-221	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-222	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado
11130-223	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-224	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-225	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado
11130-257	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-258	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-259	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado

11130-260	Light Grey	RAL 7035	1000mm	1	2	Pintura electrostática com Acabamento Texturado
11130-261	Light Grey	RAL 7035	1000mm	1	3	Pintura electrostática com Acabamento Texturado
11130-262	Light Grey	RAL 7035	1000mm	1	4	Pintura electrostática com Acabamento Texturado
11130-269	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-270	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-271	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado
11130-272	Light Grey	RAL 7035	1200mm	1	2	Pintura electrostática com Acabamento Texturado
11130-273	Light Grey	RAL 7035	1200mm	1	3	Pintura electrostática com Acabamento Texturado
11130-274	Light Grey	RAL 7035	1200mm	1	4	Pintura electrostática com Acabamento Texturado

Table 3/3

Número de catálogo	Material	Static Load
--------------------	----------	-------------

11130-202	Aço	800kg
11130-203	Aço	800kg
11130-204	Aço	800kg
11130-205	Aço	800kg
11130-206	Aço	800kg
11130-207	Aço	800kg
11130-208	Aço	800kg
11130-209	Aço	800kg
11130-210	Aço	800kg
11130-211	Aço	800kg
11130-212	Aço	800kg
11130-213	Aço	800kg
11130-214	Aço	800kg
11130-215	Aço	800kg
11130-216	Aço	800kg
11130-217	Aço	800kg
11130-218	Aço	800kg
11130-219	Aço	800kg
11130-220	Aço	800kg

11130-221	Aço	800kg
11130-222	Aço	800kg
11130-223	Aço	800kg
11130-224	Aço	800kg
11130-225	Aço	800kg
11130-257	Aço	800kg
11130-258	Aço	800kg
11130-259	Aço	800kg
11130-260	Aço	800kg
11130-261	Aço	800kg
11130-262	Aço	800kg
11130-269	Aço	800kg
11130-270	Aço	800kg
11130-271	Aço	800kg
11130-272	Aço	800kg
11130-273	Aço	800kg
11130-274	Aço	800kg

DETALHES ADICIONAIS DO PRODUTO

Side panel must be ordered separately. For suitable cable panel see Accessories.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE