


# ABS Adjustable Busbar Support Profile



## CERTIFICATIONS



## CARACTERISTICAS

For use with ABS Adjustable Busbar Support Insulator Modules

Drill holes in field for custom distances between phases

Improve bending resistance by interlocking or stacking two profiles

Attach profiles together or attach profile to the panel structure using ABS Adjustable Busbar Support Profile Stiffener


RoHS compliant

## ESPECIFICAÇÕES

Table 1/1

| Número de catálogo | Número do artigo | Material | Length (L) | Altura (H) | Largura (W) | Peso unitário |
|--------------------|------------------|----------|------------|------------|-------------|---------------|
| ABS-AP             | 560940           | Aluminio | 2m         | 23 mm      | 47 mm       | 1.37 kg       |

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência  
técnica

### Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

### Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

### APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE