

nVent ERIFLEX Flexbus Foam Barrier FBS



CERTIFICATIONS



CARACTERISTICAS

Easy access for difficult-to-reach openings

Age, smoke and damp resistant

Re-enterable and repairable

Excellent adhesion

No backing material required

F-rating / E-rating up to 2 hours

T-rating / I-rating up to 2 hours

Expands up to 5 times of its volume

ESPECIFICAÇÕES

Temperatura da instalação:	15 to 30 °C
Volume:	380ml
Largura:	450 mm Max
Altura:	500 mm Max
Approx. Cure Time:	90 s Min

Table 1/2

Número de catálogo	Número do artigo	Cor	Em conformidade com	Density	Flammability Rating	Sound Transmission Class
FLEXFOAMBAR UL	508153	Vermelho, Brown	ASTM E 84 (UL 723), ASTM E 814 (UL 1479)			
FLEXFOAMBARRIER	508150	Vermelho, Brown	EN 13501-1, EN 1366-3	215 kg/m³ Min	DIN 4102 (B2)	43.5 - 66 dB(A)

Table 2/2

Número de catálogo	Número do artigo	Volume Yield	Peso unitário	Certifications
FLEXFOAMBARUL	508153	1.9 l Max	0.72 kg	CE, cULus Classified, ESTI ERIFLEX Flexbus, RoHS
FLEXFOAMBARRIER	508150	2.1 l Max	0.72 kg	ESTI ERIFLEX Flexbus, RoHS, FBS-EN, CE

DETALHES ADICIONAIS DO PRODUTO

The thickness of the penetration seal has to be minimum 200mm, depending on the fire resistance classification (see Annex J-1 of the ETA) in order to obtain EI120 fire-resistance.

If 200mm is not possible, the FIB (intumescent wrap) needs to be used around the Flexbus Conductors and with 150mm width on both sides in order to reach EI120 fire resistance.

The width and height is referring to the maximum opening size of the penetration seal.

The total cross section of the installation (including insulation and conductor) must not be more than 60% of the opening size of the penetration seal.

The first support for the Flexbus Conductor has to be at a maximum 200mm measured from the surface of the penetration seal.

The Flexbus Foam Barrier FBS has to be used with the FFBD Foam Dispenser.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE