

Aço inoxidável, individual, monobloco, SSFS



This single-door enclosure provides industry-leading protection for systems incorporating large components or complex mounting configurations in highly corrosive environments. The addition of 19-in. rack-mounting accessories makes these enclosures ideal for providing rugged protection for sensitive rack-mounted components in harsh industrial environments. The enclosure is typically used in food-processing plants, pharmaceutical manufacturing facilities, petrochemical plants and waste-water treatment facilities.

NORMAS DA INDÚSTRIA

IEC EN 60529, IP66
IEC EN 50102, IK10
IEC EN 62208;
UL 508A Listed;
Type 4, 4X, 12 File No. E61997
NEMA Type 4, 4X, 12

CARACTERÍSTICAS

Two-door enclosures are provided with a removable centerpost for easy mounting plate installation

Seamless foam-in-place polyurethane gasket assures a water-tight and dust-tight seal

High-impact thermoplastic data pocket provided with each enclosure

Base plinth 100 mm included, with front and rear removable cover for easy cable entry

External surface body and door brushed finish grain 240, Ra less than or equal to 0,8 um, smooth internal surface (2B)

Heavy-duty three-point latching mechanism operated by Type 316L stainless steel PowerGlide padlocking handle

Seams continuously welded and ground smooth

Body grounding, studs door and body

Bottom gland plates, 3,0 mm removable from inside, with grounding stud

Door opening angle 100 degrees

ESPECIFICAÇÕES

Espessura:	2.5mm
Acabamento:	Polido
Placa de montagem incluída:	Não
Gland Plate Included:	Sim

Table 1/1

Número de catálogo	Altura	Largura	Profundidade	Material	Altura da placa de montagem	Largura da placa de montagem
A18104SS6FS	1800mm	1000mm	400mm	Aço Inoxidável 316L	1595mm	897mm
A18104SSFS	1800mm	1000mm	400mm	Stainless Steel 304	1595mm	897mm
A18106SSFS	1800mm	1000mm	600mm	Stainless Steel 304	1595mm	897mm
A18124SSFS	1800mm	1200mm	400mm	Stainless Steel 304	1595mm	1097mm
A18126SSFS	1800mm	1200mm	600mm	Stainless Steel 304	1595mm	1097mm
A1864SSFS	1800mm	600mm	400mm	Stainless Steel 304	1595mm	497mm
A1866SSFS	1800mm	600mm	600mm	Stainless Steel 304	1595mm	497mm
A1884SSFS	1800mm	800mm	400mm	Stainless Steel 304	1595mm	697mm
A1886SSFS	1800mm	800mm	600mm	Stainless Steel 304	1595mm	897mm
A20106SSFS	2000mm	1000mm	600mm	Stainless Steel 304	1795mm	897mm
A20108SS6FSDA	2000mm	1000mm	800mm	Aço Inoxidável 316L	1795mm	897mm
A20108SSFS	2000mm	1000mm	800mm	Stainless Steel 304	1795mm	897mm
A20126SSFS	2000mm	1200mm	600mm	Stainless Steel 304	1795mm	1097mm
A20128SS6FSDA	2000mm	1200mm	800mm	Aço Inoxidável 316L	1795mm	1097mm
A20128SSFS	2000mm	1200mm	800mm	Stainless Steel 304	1795mm	1097mm
A20128SSFSDA	2000mm	1200mm	800mm	Stainless Steel 304	1795mm	1097mm

Número de catálogo	Altura	Largura	Profundidade	Material	Altura da placa de montagem	Largura da placa de montagem
A20168SS6FSDA D	2000mm	1560mm	800mm	Aço Inoxidável 316L	1795mm	1463mm
A20168SSFS	2000mm	1560mm	800mm	Stainless Steel 304	1795mm	1463mm
A20168SSFSDA	2000mm	1560mm	800mm	Stainless Steel 304	1795mm	1463mm
A2066SSFS	2000mm	600mm	600mm	Stainless Steel 304	1795mm	497mm
A2068SSFS	2000mm	600mm	800mm	Stainless Steel 304	1795mm	497mm
A2086SSFS	2000mm	800mm	600mm	Stainless Steel 304	1795mm	697mm
A2088SS6FS	2000mm	800mm	800mm	Aço Inoxidável 316L	1795mm	697mm
A2088SS6FSDA	2000mm	800mm	800mm	Aço Inoxidável 316L	1795mm	697mm
A2088SSFS	2000mm	800mm	800mm	Stainless Steel 304	1795mm	697mm
A2088SSFSDA	2000mm	800mm	800mm	Stainless Steel 304	1795mm	697mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE