

# CS480 Swivel Base Bracket Coupling Internal



CS480 Swivel Base Bracket Coupling Internal mounts the enclosure directly to horizontal surfaces, enabling 340-degree enclosure rotation. Base mounting hardware is hidden. Maintenance-free bearings.

## **NORMAS DA INDÚSTRIA**

---

IEC 60529, IP66

## **CARACTERÍSTICAS**

---

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

## ESPECIFICAÇÕES

| Table 1/1          |        |         |              |                     |            |              |
|--------------------|--------|---------|--------------|---------------------|------------|--------------|
| Número de catálogo | Altura | Largura | Profundidade | Material            | Acabamento | Envio rápido |
| CCSS48BBCRI        | 110mm  | 116mm   | 116mm        | Stainless Steel 304 | Polido     | Não          |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE