

## Main busbar supports horizontal | Distribuição de energia, MSHS



This horizontal busbar support, MSHS, for two bars up to 120x10 mm, is available off the shelf and has been tested according to IEC 61439. It can be mounted at any height behind fix, modular, and plug-in systems.

## **CARACTERISTICAS**

Descrição: Busbar supports up to 3600A to be mounted horizontally behind the compartments. Mounts to the internal side panels MSPS, and in the height position which we need. Supports for single or double bar per phase for bar thickness 10 mm, and width from 10 to 120 mm. Distance between bars of 20 mm.

Material: Polycarbonate reinforced with 10% of glass material.

Fornecimento: Busbar support for 3 phases and neutral, and mounting material.

Distance between bars of 20 mm

Material: Polycarbonate reinforced with 10% of glass material

Delivery: Busbar support for 3 phases and neutral, and mounting material

Horizontal main busbar support for 2 bars up to  $120 \times 10$  mm, which can be mounted at the required height behind any system (fix, modular or plug-in)

The standard supports are available off the shelf and have been tested according to IEC 61439

The supports are suitable for the most common bars on the market

Main busbars can be installed in the middle of the enclosure height, which will reduce the required busbar section

A flexible and reliable solution that ensures procurement, design and installation can be done efficiently reducing the labour time required

Internal side panels (MSPS) are required in order to mount the busbar supports

## **ESPECIFICAÇÕES**

| Table 1/1             |        |         |                      |                     |               |            |
|-----------------------|--------|---------|----------------------|---------------------|---------------|------------|
| Número de<br>catálogo | Altura | Largura | Material do gabinete | Família de produtos | Material      | Acabamento |
| MSHS408010            | 620mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS401010            | 300mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS405010            | 540mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS406010            | 540mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS403010            | 420mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS410010            | 700mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS404010            | 460mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS412010            | 780mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |
| MSHS402010            | 380mm  | 95mm    | Aço Macio            | Free-Standing       | Policarbonato | Smooth     |

## **AVISO**

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



**HOFFMAN TRACHTE SCHROFF ILSCO**