

Porta plana | Armários de instalação no solo, DN



Esta porta substitui o painel traseiro num armário de instalação no solo para permitir o acesso pela retaguarda ao equipamento instalado na dianteira ou para utilizar placas de montagem com as partes posteriores encostadas, de forma a aumentar o espaço de montagem do armário.

CARACTERISTICAS

Descrição: Porta padrão equipada com sistema de trava de 3 mm e porta dupla. O kit de acessórios de porta DNMK (dobradiças, hastes de haste) deve ser pedido separadamente. Permite todas as opções do programa de travamento e dobradiças de 180 °. Compatível com faixas de gabinetes combináveis e compactas.

Material: Chapa de aço de 2 mm de espessura.

Carga máxima: 800 N.

Acabamento: Pintura electrostática a pó em RAL 7035 com acabamento texturado.

Requisitos de montagem: Se de antemão não tiver porta utilize o kit de dobradiças DNMK.

Quantidade por embalagem: 1 Porta.

ESPECIFICAÇÕES

Cor:	Light Gray
Material:	Aço Macio
Acabamento:	Pintura electrostática com Acabamento Texturado
Código de cor:	RAL 7035

Table 1/1						
Número de catálogo	Altura	Largura	Profundidade	Door Type	Material do gabinete	Família de produtos
DN2210R5	2182mm	993mm	17mm	Plain	Aço Macio	Free-Standing
DN1106R5	1082mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN1206LR5	1182mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN1206R5	1182mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN1206RR5	1182mm	593mm	17mm	Right Door	Aço Macio	Free-Standing
DN1208R5	1182mm	793mm	17mm	Plain	Aço Macio	Free-Standing
DN1405LR5	1382mm	493mm	17mm	Left Door	Aço Macio	Free-Standing
DN1405RR5	1382mm	493mm	17mm	Right Door	Aço Macio	Free-Standing
DN1406LR5	1382mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN1406R5	1382mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN1406RR5	1382mm	793mm	17mm	Right Door	Aço Macio	Free-Standing
DN1408R5	1382mm	793mm	17mm	Plain	Aço Macio	Free-Standing
DN1606LR5	1582mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN1606R5	1582mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN1606RR5	1582mm	593mm	17mm	Right Door	Aço Macio	Free-Standing
DN1608R5	1582mm	793mm	17mm	Plain	Aço Macio	Free-Standing

Número de catálogo	Altura	Largura	Profundidade	Door Type	Material do gabinete	Família de produtos
DN1610R5	1582mm	993mm	17mm	Plain	Aço Macio	Free-Standing
DN1804LR5	1782mm	393mm	17mm	Left Door	Aço Macio	Free-Standing
DN1804RR5	1782mm	393mm	17mm	Right Door	Aço Macio	Free-Standing
DN1805LR5	1782mm	493mm	17mm	Left Door	Aço Macio	Free-Standing
DN1805R5	1782mm	493mm	17mm	Plain	Aço Macio	Free-Standing
DN1805RR5	1782mm	493mm	17mm	Right Door	Aço Macio	Free-Standing
DN1806LR5	1782mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN1806R5	1782mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN1806RR5	1782mm	593mm	17mm	Right Door	Aço Macio	Free-Standing
DN1808LR5	1782mm	793mm	17mm	Left Door	Aço Macio	Free-Standing
DN1808R5	1782mm	793mm	17mm	Plain	Aço Macio	Free-Standing
DN1808RR5	1782mm	793mm	17mm	Right Door	Aço Macio	Free-Standing
DN1810R5	1782mm	993mm	17mm	Plain	Aço Macio	Free-Standing
DN2004LR5	1982mm	393mm	17mm	Left Door	Aço Macio	Free-Standing
DN2004RR5	1982mm	393mm	17mm	Right Door	Aço Macio	Free-Standing
DN2005LR5	1982mm	493mm	17mm	Left Door	Aço Macio	Free-Standing
DN2005R5	1982mm	493mm	17mm	Plain	Aço Macio	Free-Standing
DN2005RR5	1982mm	493mm	17mm	Right Door	Aço Macio	Free-Standing
DN2006LR5	1982mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN2006R5	1982mm	593mm	17mm	Plain	Aço Macio	Free-Standing

Número de catálogo	Altura	Largura	Profundidade	Door Type	Material do gabinete	Família de produtos
DN2006RR5	1982mm	593mm	17mm	Right Door	Aço Macio	Free-Standing
DN2008LR5	1982mm	793mm	17mm	Left Door	Aço Macio	Free-Standing
DN2008R5	1982mm	793mm	17mm	Plain	Aço Macio	Free-Standing
DN2008RR5	1982mm	793mm	17mm	Right Door	Aço Macio	Free-Standing
DN2010R5	1982mm	993mm	17mm	Plain	Aço Macio	Free-Standing
DN2205LR5	2182mm	493mm	17mm	Left Door	Aço Macio	Free-Standing
DN2205RR5	2182mm	493mm	17mm	Right Door	Aço Macio	Free-Standing
DN2206LR5	2182mm	593mm	17mm	Left Door	Aço Macio	Free-Standing
DN2206R5	2182mm	593mm	17mm	Plain	Aço Macio	Free-Standing
DN2206RR5	2182mm	593mm	17mm	Right Door	Aço Macio	Free-Standing
DN2208R5	2182mm	793mm	17mm	Plain	Aço Macio	Free-Standing
DN1804R5	1782mm	393mm	17mm	Plain	Aço Macio	Free-Standing
DN2004R5	1982mm	393mm	17mm	Plain	Aço Macio	Free-Standing
DN2204R5	2182mm	393mm	17mm	Plain	Aço Macio	Free-Standing

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE