

Acoplamento cotovelo HMI, ligeiro, S1MFEC



Suspend 180-Max Flange Elbow Coupling attaches directly to the enclosure for applications where a vertical tube is not required. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The flange elbow coupling has a safety stop and maintenance-free bearings.

CARACTERISTICAS

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

ESPECIFICAÇÕES

Material: Alumínio
Acabamento: Pintura electrostática com Acabamento Texturado

Table 1/1						
Número de catálogo	Altura	Largura	Profundidade	Cor	Código de cor	Envio rápido
S1MFECG	138mm	125mm	124mm	Light Gray	RAL 7035	Não
S1MFEC	138mm	195mm	125mm	Jet Black	RAL 9005	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE