

Kit acoplam. cotovelo, S2MFEC



Suspend 281-Max Flange Elbow Coupling attaches directly to the enclosure for applications where a vertical tube is not required. Enables enclosure to be rotated 300 degrees and locked in position. Includes safety stop and maintenance-free bearing.

CARACTERISTICAS

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

Gray plastic cable access cover is included

Assembled Suspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

ESPECIFICAÇÕES

Table 1/1						
Número de catálogo	Altura	Largura	Profundidade	Material	Acabamento	Cor
S2MFEC	137mm	214mm	108mm	Aluminio	Pintura electrostática com Acabamento Texturado	Jet Black

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE