

Pedestal de movimento vertical, S2M10VP



Syspend 281-Max Vertical Motion Pedestal Tube is a vertical adjustable tube with a lift range of 250mm, allowing enclosure to be positioned at the optimal viewing height for different operators. The 48-mm Round Tube Flange Coupling (S2MFC48) and Adapter (S2MA48) is required for attachment to HMI enclosures with a 60 x 60-mm hole pattern (i.e. Syspend Aluminum HMI and Concept HMI). The weight of the coupling, adapter plate, enclosure and internal components must be factored into the load when selecting a tube.

CARACTERISTICAS

Adjustable from 1130 mm (44.49 in.) to 1380 mm (54.33 in.) with internal gas springs

Four models support loads ranging from 11 to 77 lb. (4.9 to 34.9 kg)

Height is fixed in place at any position by locking handle

Cables are separated from gas springs inside the tube

Internal strain-relief for cables inside the tube

Can be attached to Small Pedestal Base, Vertical Wall Joint, Wall Flange, Rotary Base, Elbow or Rotatable Elbow

Tube cannot be inverted for overhead mounting on the enclosure

ESPECIFICAÇÕES

Material: Alumínio
Acabamento: Anodized

Table 1/1						
Número de catálogo	Altura	Largura	Profundidade	Espessura	Max L	Min L
S2M10VP57	1380mm	70mm	90mm	6mm	350mm	100mm
S2M10VP77	1380mm	70mm	90mm	6mm	350mm	100mm
S2M10VP22	1380mm	70mm	90mm	6mm	350mm	100mm
S2M10VP37	1380mm	70mm	90mm	6mm	350mm	100mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE