

nVent LENTON Interlok HYA15HT Grout Additive, Hot Temperature



The nVent LENTON HYA15LM Grout Additive, Hot Temperature is designed to be used in conjunction with nVent LENTON Interlok grout-fill couplers and nVent LENTON Interlok HY15LM Grout. The additive is used to increase working time of the grout during hot temperature applications which allows for a longer time window to place the grout into the Interlok couplers. This proprietary grout additive increases the maximum working temperature of HY15LM grout from 100 °F (38 °C) to 122 °F (50 °C).

CARACTERÍSTICAS

Allows for hot temperature grouting

Increases grout working time in hot climates

Extends the construction season

For use in pump or gravity fill applications

ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Compressive Strength	Temperatura de trabalho	Peso unitário
HYA15HT	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	21 to 50 °C	0.05 kg

DETALHES ADICIONAIS DO PRODUTO

For use with HY15LM grout only.

Hot weather concreting procedures, such as ACI 305 Hot Weather Concreting, must be followed.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

HYA15HT can be used in temperatures as low as 70 °F (21 °C) to extend working time; however, this may slow the compressive strength curve.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE