

19" Pusher Fan, 2 U, Axial

Concessionárias de energia

Fan tray with integrated pusher fan.



CERTIFICAÇÕES



RECURSOS

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

ESPECIFICAÇÕES

Table 1/1

Número do catálogo	Input Voltage AC	Input Voltage DC
10713-518	230 V min	
10713-520	115 V min	

Número do catálogo	Input Voltage AC	Input Voltage DC
10713-526	230 V min	
10713-534	230 V min	
10713-536	115 V min	
10713-529		24 V min
10713-537		24 V min
19713-540		

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE