


19" Pusher Fan, 3 U, Axial

Concessionárias de energia

Fan tray with integrated pusher fan.



CERTIFICAÇÕES



RECURSOS

Ventilation directed accurately to the electronics

19" Pusher Fan, 3 U, Axial

Air infeed from front, air exits at the top rear of cabinet (guided upwards by cover plates or via hoses to rear and upwards)

Contact protection in accordance with DIN EN ISO 13857

ESPECIFICAÇÕES

Table 1/1

Número do catálogo	Input Voltage AC
10713-546	230 V min
10713-547	115 V min

ADDITIONAL PRODUCT DETAILS

With cover plates, this pusher fan can be re-fitted to different cooling concepts

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE