

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

NÚMERO DE CATÁLOGO

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

CARACTERÍSTICAS

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

CARATERÍSTICAS DO PRODUTO

Product Type: Cabinet Door

Família de produtos: Varistar CP

Tipo: Steel Door, Perforated

Works With: Varistar CP

Locking Type: Single Point Locking

Cor: Black Grey

Código de cor: RAL 7021

Rack Height: 29 U

Altura: 1400 mm

Largura: 800 mm

Grau de proteção: IP20

Em conformidade com: IEC 61587-1

DETALHES ADICIONAIS DO PRODUTO

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE