

Modular Single Door, MCSS

Concessionárias de energia



The stainless steel single door modular floor standing enclosure range, MCSS, with a IP 55 protection degree, is available off the shelf in many different sizes. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure. This enclosure range is well suited for almost any environment, grade dependent.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E92044

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E92044

NEMA/EEMAC Type 12

CSA, File No. 1442951: Tipo 12

IEC 62208 IP55

KEMA, GOST, Lloyds, CE, EAC

RECURSOS

Estrutura: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660

Porta: Mounted with four hinges allowing left or right hand opening; including door frame with 25 mm hole pattern

Painel traseiro: Fitted by M6 torx screws; standard facilities for rear door mounting

Supplied as an accessory

Removable roof panel

Lock: Espagnolette 4-point locking system which does not interfere with the enclosure inner space; standard double-bit 3 mm insert

Bottom plate: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing

Mounting plate: Double folded and slides into position with adjustable depths of 25 mm, with the MPD02 accessory

Earthing/Grounding: All panels are earthed/grounded through their fittings and equipped with a separate earthing stud

Mounting requirements: Standard delivery ready for combined installation; for stand-alone installation, add side panels

Delivery: Frame with fitted door, rear panel, roof panel, bottom plate, mounting plate and door frame; delivery also includes earthing bolts

ESPECIFICAÇÕES

Body Thickness:	1,5 mm
Door Thickness:	2 mm
Acabamento:	Brushed
Material:	Aço inoxidável
Cor:	Unpainted

Table 1/1				
Número do catálogo	Número do artigo	Altura	Largura	Profundidade
MCSS18065	MCSS18065	1800 mm	600 mm	500 mm
MCSS18085	MCSS18085	1800 mm	800 mm	500 mm
MCSS20066	MCSS20066	2000 mm	600 mm	600 mm
MCSS20086	MCSS20086	2000 mm	800 mm	600 mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE