

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Concessionárias de energia



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICAÇÕES



RECURSOS

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Profundidade	Usable Width	Instalação	Em conformidade com	EMC Shielding
20860-621	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-622	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-624	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-625	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-626	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-627	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-628	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-629	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-630	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-632	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-633	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-634	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-635	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Número do catálogo	Product Family	Product Type	Tipo	Certificações
20860-621	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-622	MultipacPRO	Subrack/Chassis	Perforated	RoHS

Número do catálogo	Product Family	Product Type	Tipo	Certificações
20860-624	MultipacPRO	Subrack/Chassis	Perforated	
20860-625	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-626	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-627	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-628	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-629	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-630	MultipacPRO	Subrack/Chassis	Perforated	
20860-632	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-633	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-634	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-635	MultipacPRO	Subrack/Chassis	Perforated	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE