

# MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

## Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

## CERTIFICATIONS



## CARACTERISTICAS

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Rack Height | Profundidade | Usable Width | Instalação | Em conformidade com              | EMC Shielding      |
|--------------------|-------------|--------------|--------------|------------|----------------------------------|--------------------|
| 20860-601          | 1 U         | 220 mm       | 403 mm       | Rack       | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-602          | 1 U         | 280 mm       | 403 mm       | Rack       | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-603          | 1 U         | 340 mm       | 4 mm         | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-604          | 2 U         | 220 mm       | 4 mm         | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-605          | 2 U         | 280 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-606          | 2 U         | 340 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-607          | 3 U         | 280 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-608          | 3 U         | 340 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-609          | 3 U         | 400 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-610          | 3 U         | 460 mm       | 4 mm         | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-611          | 4 U         | 280 mm       | 4 mm         | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-612          | 4 U         | 340 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-613          | 4 U         | 400 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-614          | 4 U         | 460 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-615          | 5 U         | 460 mm       | 403 mm       | Rack       | IEC 60297-3-100                  | No (Retrofittable) |

Table 2/2

| Número de catálogo | Família de produtos | Product Type | Tipo | Certifications |
|--------------------|---------------------|--------------|------|----------------|
|--------------------|---------------------|--------------|------|----------------|

|           |             |                 |       |      |
|-----------|-------------|-----------------|-------|------|
| 20860-601 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-602 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-603 | MultipacPRO | Subrack/Chassis | Solid |      |
| 20860-604 | MultipacPRO | Subrack/Chassis | Solid |      |
| 20860-605 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-606 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-607 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-608 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-609 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-610 | MultipacPRO | Subrack/Chassis | Solid |      |
| 20860-611 | MultipacPRO | Subrack/Chassis | Solid |      |
| 20860-612 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-613 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-614 | MultipacPRO | Subrack/Chassis | Solid | RoHS |
| 20860-615 | MultipacPRO | Subrack/Chassis | Solid | RoHS |

## DETALHES ADICIONAIS DO PRODUTO

Please order front handles separately.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos

à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**