

RackPower 3x Temperature and 1x Humidity Sensor

Concessionárias de energia

3x Temperature and 1x Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

RECURSOS

3x Temperature and 1x Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +/- 5 %

Second and Third Temperature Sensor with 950 mm cable

ESPECIFICAÇÕES

Table 1/1

Número do catálogo	Tipo	Works With
EA9105	Temperature and Humidity	RackPower

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE