

RackPower Basic PDU, RB0xxx, 230 VAC, 1-phase

Concessionárias de energia

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

RECURSOS

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Input connector IEC 60309 332P6

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Product Type	Socket Type	Cor	Comprimento	Voltage AC	Profundidade
RB0328	Socket Strip	IEC C13, IEC C19	Preto	1490 mm	230 V	53 mm

Table 2/2

Número do catálogo	Largura
RB0328	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE