

RackPower PDU, RP2xxx, 100-240 VAC, 1-phase

Concessionárias de energia

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

RECURSOS

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13, C19 outlets

User-defined power-on time delay or automatic power-on sequencing

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Product Type	Socket Type	Cor	Comprimento	Voltage AC	Function
RP2326	Socket Strip	IEC C13, IEC C19	Preto	1490 mm	230 V	Input Monitored, Switched Outlets

Table 2/2

Número do catálogo	Profundidade	Largura
--------------------	--------------	---------

RP2326	53 mm	52 mm
--------	-------	-------

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE