

Varistar CP Double Steel Door, Perforated, 3-Point Locking

Concessionárias de energia

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

RECURSOS

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Em conformidade com
21630-020	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-021	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-022	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-027	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-028	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-029	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Em conformidade com
21630-448	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-449	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-450	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-451	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-452	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-453	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-454	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-455	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Número do catálogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-020	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-448	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

Número do catálogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-450	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-451	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-452	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE