

# Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

## Concessionárias de energia

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

### RECURSOS

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

### ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Em conformidade com
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Número do catálogo	Acabamento	Locking Type	Material	Product Type	Protection Rating	Tipo
21630-820	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Número do catálogo	Works With
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## AVISO

---

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**