

Varistar CP Mobile Base/Plinth

Concessionárias de energia

Mobile base/plinth to make a cabinet mobile.

RECURSOS

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1000 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Largura	Profundidade	Cor	Color Code	Product Type	Tipo
21630-655	600 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-656	600 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-657	600 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-658	600 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-661	800 mm	600 mm			Cabinet/Rack Base	Base Plinth, Mobile
21630-662	800 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-663	800 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile

Número do catálogo	Largura	Profundidade	Cor	Color Code	Product Type	Tipo
21630-664	800 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile

Table 2/2

Número do catálogo	Works With
21630-655	Varistar CP
21630-656	Varistar CP
21630-657	Varistar CP
21630-658	Varistar CP
21630-661	Varistar CP
21630-662	Varistar CP
21630-663	Varistar CP
21630-664	Varistar CP

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE