

Varistar CP Steel Door, Perforated With 3-Point Electronic Locking

Concessionárias de energia

Varistar CP perforated steel door 3-point locking for IP 20 applications.

RECURSOS

Perforated steel door with 3-point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Altura	Largura	Tipo	Cor	Color Code
21630-814	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-815	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-816	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-817	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-818	47 U	2200 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-819	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-895	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-896	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021

Número do catálogo	Rack Height	Altura	Largura	Tipo	Cor	Color Code
21630-897	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-898	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-899	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-900	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021

Table 2/3						
Número do catálogo	Em conformidade com	Acabamento	Locking Type	Material	Product Type	Protection Rating
21630-814	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-815	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-816	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-817	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-818	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-819	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-895	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-896	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-897	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-898	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-899	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20
21630-900	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Aço	Cabinet Door	IP20

Table 3/3

Número do catálogo	Works With
21630-814	Varistar CP
21630-815	Varistar CP
21630-816	Varistar CP
21630-817	Varistar CP
21630-818	Varistar CP
21630-819	Varistar CP
21630-895	Varistar CP
21630-896	Varistar CP
21630-897	Varistar CP
21630-898	Varistar CP
21630-899	Varistar CP
21630-900	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE