


ACS-30 Sensing and Monitoring Module



The nVent RAYCHEM ACS-30-EU-ELEXANT650C-SMDI-MOD Module for the ACS-30 system provides smart sensor input for surface snow melting and roof & gutter de-icing applications. The Remote Monitoring Module (RMM) is used to collect sensor/temperature inputs for monitoring of the heat tracing circuits of an ACS-30 control system.

RECURSOS

The output from the ACS-30-EU-ELEXANT650C-SMDI-MOD module enables the switching of the heating circuits within the power & control module (PCM)

The ACS-30-EU-ELEXANT650C-SMDI-MOD module provides ground or roof & gutter temperature and moisture sensing for the ACS-30 control system

Ground temperature and moisture sensor (E650C-G) and roof & gutter temperature and moisture sensor (E650C-R) are sold separately

The RMM provides up to 8 sensor inputs per module with feedback to the ACS-30-EU-UIT3 interface

A single twisted pair RS-485 cable connects up to 247 RMM units providing additional temperature monitoring sensor inputs

The RMM is remotely located adjacent to the desired measurement locations

The RMM comes in 2 versions: ACS-30-EU-RMM3 (230 V) and ACS-30-EU-RMM3-24VDC (24 V), both pre-installed inside a compact enclosure

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Nome do item	Profundidade	Altura	Housing Material	Classificação IP	Instalação
2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	132 mm	262 mm	Polycarbonato	IP20	Wall Mounted

Table 2/2

Número do catálogo	Nome do item	Largura
--------------------	--------------	---------

2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	332 mm
------------	--------------------------------	--------

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT