

Low-Profile Connection Kit for Parallel Heating Cables, Cold-Applied, ATEX



nVent RAYCHEM C-150-E is a cold-applied, low profile, under insulation power connection to flexible power cable, for use with nVent RAYCHEM BTV, QTVR, XTV and KTV. It can be used in applications with temperature ratings from -50 °C to 215 °C.

RECURSOS

Simple and fast to install

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

One low profile, under-insulation component for all nVent RAYCHEM industrial self-regulating heating cables

Simplified design in hazardous area, integral part of system approval

Reliable during long life: 10 year extended product warranty available, maintenance free

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Nome do item	Model	Tipo de conexão	Voltage Rating	Current Rating	Max Exposure Temperature
073704-000	C-150-E	Heating Cable/Connection Cable	Cold Applied	277 V	25 A	215 °C

Table 2/2

Número do catálogo	Nome do item	Classificação IP	Suitable for Cold Lead
073704-000	C-150-E	IP66	7.8 – 12.5 mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos

representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT