

NGC-40 Series, Bridge Module



nVent RAYCHEM NGC-40 Series - Bridge Module provides the interface between a panel's internal CAN-based network and upstream devices. Multiple communication ports are supported, allowing serial and ethernet connections to be used with external devices: Each has two RS-485 ports, one RS-232 port and one 10/100 Base-T ethernet network with programmable communication parameters. A maximum of 80 NGC-40 modules, a combination of HTC, HTC3 or input/output modules, can be connected to one NGC-40-BRIDGE module.

RECURSOS

Provides the interface between the NGC-40 system and any upstream devices

Also used to communicate with other HTC modules in the NGC-40 system

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Nome do item	Voltage Rating	Voltage Rating Type	Operating Temperature	Supporting Protocol, CAN	Module Quantity
10730-002	NGC-40-BRIDGE	24 V	DC	-40 to 65 °C	Sim	80

Table 2/2

Número do catálogo	Nome do item	Altura	Largura	Profundidade
10730-002	NGC-40-BRIDGE	87 mm	45 mm	106.4 mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT