

SBS Control Panel for Hot Water Temperature Maintenance



nVent RAYCHEM SBS-XX-HX-ECO-10 control panel provides an integrated solution for nVent RAYCHEM self-regulating heating cables in single pipe hot water temperature maintenance applications. It includes the energy efficient HWAT-ECO control system and offers multi-circuit, multi-sensor and multi-control with integrated electrical protection. A 400 VAC (3 phase) supply is required.

RECURSOS

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 1-9 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: with HWAT-ECO control system integrated (providing standard, economy, and 'tap time' set-back timer functions)

System monitoring, with alarm functions, including monitoring of boiler output temperature and low temperature alarm

Reliable, a complete system from one manufacturer, specifically designed for single pipe hot water temperature maintenance applications

Reliable during long life: 6 year extended product warranty available, maintenance free

ESPECIFICAÇÕES

Classificação IP: IP65

Instalação: Wall Mounted

Table 1/2

Número do catálogo	Nome do item	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Altura
035958-000	SBS-03-HV-ECO-10	3	20 A, Type C	32 A	1	600 mm

Número do catálogo	Nome do item	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Altura
539268-000	SBS-06-HV-ECO-10	6	20 A, Type C	63 A	2	600 mm
294452-000	SBS-09-HV-ECO-10	9	20 A, Type C	63 A	3	600 mm

Table 2/2

Número do catálogo	Nome do item	Largura	Profundidade
035958-000	SBS-03-HV-ECO-10	400 mm	210 mm
539268-000	SBS-06-HV-ECO-10	600 mm	210 mm
294452-000	SBS-09-HV-ECO-10	600 mm	210 mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT