

# TT1000 Water Sensing Cable, Modular



nVent RAYCHEM TraceTek TT1000-XX-PC are a range of fixed length water sensing cables with factory installed plastic connectors. Mainly used in commercial building applications, it is typically intended for leak detection under raised floors, in mechanical rooms and similar flat surface areas. It detects the presence of water at any point along its length. Installed with an alarm and locating module, the cable senses water leaks, triggers an alarm and pinpoints the location.

## RECURSOS

Advanced technology: rugged conductive polymer and fluoropolymer construction, resistant to corrosion and abrasion

Simple and fast to install: small, lightweight and flexible

Easy to design, fast drying, and reuseable

Distributed leak detection and location over a wide range of areas

Reliable and durable, 10 year product warranty available

## ESPECIFICAÇÕES

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| <b>Diâmetro externo:</b>          | 6 mm                                  |
| <b>Max Operating Temperature:</b> | 75 °C                                 |
| <b>Detection Method:</b>          | Raychem Conductive-Polymer Technology |
| <b>Detection:</b>                 | Water                                 |

Table 1/1

| Número do catálogo | Nome do item        | Comprimento |
|--------------------|---------------------|-------------|
| 017859-000         | TT1000-7.5M/25FT-PC | 7.5 m       |
| 072827-000         | TT1000-5M/17FT-PC   | 5 m         |
| 391887-000         | TT1000-3M/10FT-PC   | 3 m         |
| 396807-000         | TT1000-30M/100FT-PC | 30 m        |

| Número do catálogo | Nome do item         | Comprimento |
|--------------------|----------------------|-------------|
| 409271-000         | TT1000-1M/3FT-PC     | 1 m         |
| 805147-000         | TT1000-15M/50FT-PC   | 15 m        |
| P000000702         | TT1000-100M/330FT-PC | 100 m       |
| P000000864         | TT1000-25M/82FT-PC   | 25 m        |
| P000000873         | TT1000-50M/165FT-PC  | 50 m        |
| P000001222         | TT1000-6M/20FT-PC    | 6 m         |
| P000001223         | TT1000-10M/33FT-PC   | 10 m        |
| P000001224         | TT1000-12M/39FT-PC   | 12 m        |
| P000001225         | TT1000-30M/98FT-PC   | 30 m        |
| P000001226         | TT1000-45M/147FT-PC  | 45 m        |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

**América do Norte**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**América Latina**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**