

WinterGard Cable



nVent RAYCHEM WinterGard Cable is a constant output trace heating cable for simple, fast and effective ramp and access way heating to prevent snow and ice formation. It is designed for applications where 230 or 400 VAC supply is available. Pre-terminated.

RECURSOS

Simple to design: variable power output dependent upon cable spacing, up to 300 W/m², variety of sizes available to meet project requirements

Easy to install: flexible, excellent for irregular shaped areas, pre-terminated

Safe and efficient in operation through advanced energy saving controls

Reliable during long life: 10 year product warranty available, maintenance free

For embedding in concrete, sand bed or in asphalt

ESPECIFICAÇÕES

Min Installation Temperature:	5 °C
Cold Lead Length:	5 m
Diâmetro externo:	7 mm
Min Bending Radius:	50 mm
Max Continuous Exposure Temperature, Power Off:	65 °C
Cor:	Preto
Heating Cable Technology:	Constant Wattage
Ground Path Type:	Foil and Drainwire
Area Classification:	Non-Hazardous
Outer Jacket Material:	Poliolefina

Table 1/1

Número do catálogo	Nome do item	Nominal Voltage	Nominal Power Output @ 230V	Nominal Power Output @ 400V	Comprimento
1244-022761	WINTERGARD-CABLE-400V-26M	400 V		30 W/m	26 m

Número do catálogo	Nome do item	Nominal Voltage	Nominal Power Output @ 230V	Nominal Power Output @ 400V	Comprimento
1244-022762	WINTERGARD-CABLE-400V-35M	400 V		30 W/m	35 m
1244-022763	WINTERGARD-CABLE-400V-62M	400 V		30 W/m	62 m
1244-022764	WINTERGARD-CABLE-400V-121M	400 V		30 W/m	121 m
1244-022765	WINTERGARD-CABLE-400V-172M	400 V		30 W/m	172 m
1244-022766	WINTERGARD-CABLE-400V-210M	400 V		30 W/m	210 m
1244-022767	WINTERGARD-CABLE-400V-250M	400 V		30 W/m	250 m
1244-022769	WINTERGARD-CABLE-230V-20M	230 V	30 W/m		20 m
1244-022770	WINTERGARD-CABLE-230V-29M	230 V	30 W/m		29 m
1244-022771	WINTERGARD-CABLE-230V-38M	230 V	30 W/m		38 m
1244-022772	WINTERGARD-CABLE-230V-47M	230 V	30 W/m		47 m
1244-022773	WINTERGARD-CABLE-230V-57M	230 V	30 W/m		57 m
1244-022774	WINTERGARD-CABLE-230V-67M	230 V	30 W/m		67 m
1244-022775	WINTERGARD-CABLE-230V-75M	230 V	30 W/m		75 m
1244-022776	WINTERGARD-CABLE-230V-84M	230 V	30 W/m		84 m
1244-022777	WINTERGARD-CABLE-230V-94M	230 V	30 W/m		94 m
1244-022778	WINTERGARD-CABLE-230V-112M	230 V	30 W/m		112 m
1244-022779	WINTERGARD-CABLE-230V-134M	230 V	30 W/m		134 m
1244-022780	WINTERGARD-CABLE-230V-150M	230 V	30 W/m		150 m

Número do catálogo	Nome do item	Nominal Voltage	Nominal Power Output @ 230V	Nominal Power Output @ 400V	Comprimento
1244-022781	WINTERGARD-CABLE-230V-168M	230 V	30 W/m		168 m

ADDITIONAL PRODUCT DETAILS

The heating cable should be installed on a stable subsurface. In suspended structures the substratum may consist of finished slabs, pre-stressed concrete or a suspended structure with poured concrete. The heating cables can be laid on all sub-surfaces including reinforcement grids/bars. In the case of poured concrete or in asphalt, it should be ensured that the surface is smooth and all sharp objects are removed. Ramps on a solid substratum do not require any additional thermal insulation. Appropriate preparations should be made for installing the temperature and moisture sensor.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT