

AC Fan

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



CARACTERISTICAS

119 mm DC fan with plug for connection cable

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Works With	Largura	Length	Altura	Tensão AC	Frequency
20713-147	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz
20700-001	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz
20713-142	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz
20713-146	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz
20713-243	19" Fan Trays	119mm	119mm	38mm	230V	50/60 Hz

Número de catálogo	Works With	Largura	Length	Altura	Tensão AC	Frequency
20713-244	19" Fan Trays	119mm	119mm	38mm	115V	50/60 Hz

Table 2/3						
Número de catálogo	Airflow @ 50 Hz	Airflow @ 60 Hz	Noise Level @ 50 Hz	Noise Level @ 60 Hz	Power @ 50 Hz	Power @ 60 Hz
20713-147	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20700-001	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20713-142	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-146	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-243	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20713-244	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W

Table 3/3				
Número de catálogo	Max Static Pressure	Temperatura ambiente	Quantidade por embalagem	Envio rápido
20713-147	41Pa	70°C	1	Não
20700-001	41Pa	70°C	1	Não
20713-142	23Pa	70°C	1	Não
20713-146	23Pa	70°C	1	Não
20713-243	73Pa	70°C	1	Não
20713-244	73Pa	70°C	1	Não

DETALHES ADICIONAIS DO PRODUTO

Please order connection cable and protective grille separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE