

ATCA Front Panel, St, Reinforced, With Spring Loading



AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

CERTIFICATIONS



CARACTERISTICAS

Configuration: Front panel with IEA handle (with/without spring loading)


ESPECIFICAÇÕES

- Profundidade (D): 1mm
- Rack Width: 6HP
- Rack Height: 8U
- Accessory Type: Front panel
- Product Type: Front Panel
- Material: Aço inoxidável

Table 1/2						
Número de catálogo	Quantidade por embalagem	Tipo de alça	Front Finish	Rear Finish	Altura (H)	Largura (W)
31596-792	1	Lever	Raw	Raw	323.15mm	29mm
31596-791	1	Plunger	Raw	Raw	323.15mm	29mm

Table 2/2	
Número de catálogo	Envio rápido
31596-792	Não
31596-791	Não

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE