

Interscale for Embedded NUC, Conduction Cooled, 34 mm, 112, mm 107 mm

NÚMERO DE CATÁLOGO

14820-701



Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICATIONS



STANDARDIZATION
GROUP FOR
EMBEDDED
TECHNOLOGIES

CARACTERÍSTICAS

Modular case consisting of 3 easy to assemble parts; body, topcover and front panel

Integrated EMC protection

Compliant with the SDT.03 embeddedNUC standard <http://www.sget.org/standards.html>

Cutouts specific for IES MB95 embeddedNUC board (<http://en.ies.de/>)

Rigid construction requires only two screws

Perforated side panels for passive cooling

Board mounting studs installed

Color RAL 7016

Other dimensions, cutout shapes or locations and screenprinting available

CARATERÍSTICAS DO PRODUTO

Product Type: Small Form Factor Case

Família de produtos: Interscale

Tipo: Desktop

Altura: 34mm

Largura: 112mm

Profundidade: 106.5mm

Material: Alumínio

Cor: Anthracite Grey

Código de cor: RAL 7016

Acabamento: Pintura electrostática com Acabamento Texturado

Grau de proteção: IP20

Cooling: Perforated

Quantidade por embalagem: 1

Net Weight: 0.175kg

DETALHES ADICIONAIS DO PRODUTO

Modified or customized cases upon request.

Only the listed Interscale accessories are compatible.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE