


Plug-In Unit Microswitch for IEL, IET Handle With Cable and Plug

NÚMERO DE CATÁLOGO

20817-606



Micro Switch for IEL or IET handle. The micro switch fits also for the Offset versions of the handle.

CERTIFICATIONS



CARACTERÍSTICAS

Plastic, PC, UL 94 V-0

Suitable mating connectors not included in scope of delivery

Max. switched current 50 mA

Electr. life $\geq 20,000$ switching cycles

Mech. life $\geq 20,000$ switching cycles

Molex connector housing

Molex crimp contact and fixing clip

CARATERÍSTICAS DO PRODUTO

Product Type: Switch

Works With: Front Panels

Material: Policarbonato

Quantidade por embalagem: 10

DETALHES ADICIONAIS DO PRODUTO

Mating connector not included in delivery. Mating connectors from Molex e.g. 53261-0319, 53048-0310, 53047-0310, 53398-0319, 51047-0300.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE