

VPX System, Rugged, 10 U, 10 Slot, Pluggable PSU

NÚMERO DE CATÁLOGO

20836-780



Rugged VPX system for 10 VPX boards 6 U, 1", 160 mm and 10 Rear I/O boards. The power for the system is supplied by a pluggable VPX power supply. A fan control module monitors the fans, the temperature and voltage.

CARACTERÍSTICAS

System designed in accordance with: MIL-STD-810F, MIL-STD-167, MIL-STD-461, IP 20

For rugged applications with increased shock and vibration resistance

PSU, 1 pluggable power supply, 1000 W, 6 U, space for a second PSU

Backplane VPX 10 slot, 6 U, in accordance with VITA 65, Backplane Profile BKP6-CEN10-11.2.4.4

100 to 240 VAC input on the back, main switch on the front of the chassis

LED voltage and fan fail indicator on the front

6 U Front card cage and 6U Rear I/O card cage, with 10 Slot VPX backplane

Prepared for Telescopic slides

Optimal EMC protection through hinged front and rear panel with integrated Honeycomp filter

CARATERÍSTICAS DO PRODUTO

Product Type: System

Number of Slots: 10

Tipo: Rugged 19" Rack Mount

Backplane Type: VPX, VITA 65

Data Transfer: 10 GbE; PCIe Gen3

Power per Slot: 50W

Tensão de entrada AC: 100 – 240V

Airflow Direction: Front to Rear

Rack Height: 10U

Power Supply Type: (1) Pluggable PSU

Power Supply Included: Sim

Rear I/O: Sim

Em conformidade com: ANSI/VITA 46.0-2019

Power: 1000W

Profundidade: 490mm

Altura: 443.7mm

Largura: 480mm

Quantidade por embalagem: 1

DETALHES ADICIONAIS DO PRODUTO

Modified systems available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE