


Hood for 19" module support

NÚMERO DE CATÁLOGO

24564-100

Hood to cover the rear side of 19" module support.



CERTIFICATIONS



CARACTERÍSTICAS

For assembly at rear on 19" module supports

Rear cut out for cable entry (351 x 40mm) cover through two brush strips

Rear hood prepared for grounding kit

Brush strip (self-adhesive): Plastic PVC (RAL7032), Bristle: Nylon black

CARATERÍSTICAS DO PRODUTO

Product Type: Cover

Família de produtos: EuropacPRO

Tipo: Rear Hood

Works With: Subracks

Rack Height: 3U

Altura: 132.5mm

Rack Width: 84HP

Largura: 431.5mm

Profundidade: 88.3mm

Material: Alumínio

Quantidade por embalagem: 1

Net Weight: 0.83kg

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE