


Front Panel With FDDI Cutout, 3 U, 14 HP, 2.5 mm, Al, RAL 7035

NÚMERO DE CATÁLOGO

30118-339

Front Panel, FDDI Cutout.



CERTIFICATIONS



CARACTERÍSTICAS

Front panel with 4 FDDI cut-outs

CARATERÍSTICAS DO PRODUTO

Product Type: Front Panel

Tipo: Front Panel without Handle

Accessory Type: Front panel

Instalação: Screw-on Front

Material: Alumínio

Front Finish: Painted

Rear Finish: Conductive

Código de cor: RAL 7035

Cor: Black Grey

Rack Height: 3U

Altura: 128.4mm

Rack Width: 14HP

Largura: 70.8mm

Profundidade: 2.5mm

Quantidade por embalagem: 1

Acabamento: Pintura electrostática com Acabamento Texturado

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE