

260 Card-Lok

NÚMERO DE CATÁLOGO

VHA260-4.80T2K



The Series 260 features a ridged shafted design which provides more uniform clamping force over the length of the Card Lok, while maintaining wedge and body alignment for easier installation.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CARACTERÍSTICAS

Weight 0.95 g/cm (0.085 oz/')

Length 96.5 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

5 segment, shafted design

DSCC 89024

Profile 6.35 mm (0.250") x 6.26 mm (0.270")

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Min expansion 8.26 mm (0.325")

Flexible mounting options

For cold wall applications

Average clamp force (4.80", black anodized) = 388 lbs

Screw actuated

Torque limiting option available; ideal for 2nd level maintenance

CARATERÍSTICAS DO PRODUTO

Product Type: PCB Retainer

Material: Alumínio

Tipo: Shafted

Thermal Performance: Better

Profile: 6.35 x 6.26 mm

Clamp Force: 136 – 181kgf

Gap Width: PCB + (7.0 - 7.9 mm)

Design Feature: Torque Limiting

DETALHES ADICIONAIS DO PRODUTO

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE