


Guide Rail End Piece, PC

Plastic end pieces for individual multi-piece guide rails with plastic or Aluminum extrusion mid-piece. Available as type Standard or Accessory.



CERTIFICATIONS



CARACTERÍSTICAS

Guide rail end pieces (PC) for individual multi-piece guide rails with plastic or aluminum extrusion mid-piece

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Mid-pieces available for standard PCB lengths (160, 220, 280 and 340 mm) and for special dimensions as 1000 mm version

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

ESPECIFICAÇÕES

Works With:	Subracks; Cases; Chassis
Família de produtos:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Material:	Fiber-Reinforced Plastic
Product Type:	Rail End Piece

Table 1/1

Número de catálogo	Quantidade por embalagem	Em conformidade com	Tipo	Unidade de embalagem	Groove Width	Envio rápido
64568-018	1	EN 45545-2	Accessory	Pair	2.5	Não
64568-004	1	EN 45545-2	Standard	Pair	2	Não
64568-014	1	EN 45545-2	Standard	Pair	2.5	Não
64568-093	1	EN 45545-2	Coding Peg	Pair	2.5	Não
64568-094	1	EN 45545-2	Coding Peg	Pair	2.5	Não
64568-095	1	EN 45545-2	Coding Peg	Pair	2.5	Não
64568-008	1	EN 45545-2	Accessory	Pair	2	Não

DETALHES ADICIONAIS DO PRODUTO

Delivery is in standard pack multiples. Pricing is per individual item.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE