


Labrack C-Rail for 19" Stationary



For assembly to the vertical uprights on the right and left hand side of the 19" plane; especially suited for cable eyes.

CERTIFICATIONS



CARACTERÍSTICAS

For assembly to the vertical uprights on the right and left hand side of the 19" plane; especially suited for cable eyes

ESPECIFICAÇÕES

Product Type: C-Rail
Material: Aço
Acabamento: Chapa de Aço Zincada

Table 1/1

Número de catálogo	Rack Height	Quantidade por embalagem	Length	Envio rápido
20118-461	24U	2	1050mm	Não
22114-461	39U	2	1650mm	Não

DETALHES ADICIONAIS DO PRODUTO

Please order assembly kit separately. Not suitable on mobile 19" lab racks.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE