

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICATIONS



CARACTERÍSTICAS

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

ESPECIFICAÇÕES

Material:	Aluminio
Acabamento:	Anodized; Passivated
Família de produtos:	MultipacPRO
EMC Shielding:	No (Retrofittable)
Tipo:	Perforated

Table 1/2

Número de catálogo	Rack Height	Profundidade	Usable Width	Instalação	Em conformidade com	Certifications
20860-621	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-622	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-624	2U	220mm	403mm	Rack	IEC 60297-3-100	
20860-625	2U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-626	2U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-627	3U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-628	3U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-629	3U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-630	3U	460mm	403mm	Rack	IEC 60297-3-100	
20860-632	4U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-633	4U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-634	4U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-635	5U	460mm	403mm	Rack	IEC 60297-3-100	RoHS

Table 2/2

Número de catálogo	Envio rápido
20860-621	Não
20860-622	Não

Número de catálogo	Envio rápido
20860-624	Não
20860-625	Não
20860-626	Não
20860-627	Não
20860-628	Não
20860-629	Não
20860-630	Não
20860-632	Não
20860-633	Não
20860-634	Não
20860-635	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front handles separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE