

Novastar Base Plate, Multi Pieces, Open at Rear



Base plate is a plain steel blanking plate fitted to the cabinet base. Restricts air-flow into the cabinet from floor cavity and can be opened for cable ducting.

CERTIFICATIONS



CARACTERÍSTICAS

Base is open at rear for cable ducting; opening can be closed with a plain or perforated cover, filter plate or brush strip

Rear opening, width 440 mm, depth 70 mm

ESPECIFICAÇÕES

Product Type: Cabinet/Rack Base

Material: Aço

Table 1/2

Número de catálogo	Largura	Profundidade	Quantidade por embalagem	Cor	Código de cor	Acabamento
--------------------	---------	--------------	--------------------------	-----	---------------	------------

27230-188	553mm	500mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-192	553mm	1000mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-191	553mm	900mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-190	553mm	800mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
27230-189	553mm	600mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado

Table 2/2

Número de catálogo	Tipo	Envio rápido
27230-188	Base Plate	Não
27230-192	Base Plate	Não
27230-191	Base Plate	Não
27230-190	Base Plate	Não
27230-189	Base Plate	Não

DETALHES ADICIONAIS DO PRODUTO

Please order cover plate or brush strip separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE