

PSU 19" AC/DC Maxpower 100 W, Triple



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and three output voltages.

CERTIFICATIONS



CARACTERÍSTICAS

Wide input voltage range 90 ... 254 V AC and 100 ... 360 VDC with active power-factor correction (PFC)

3 output voltages

Signalling: Output voltage OK

High power density

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-122	19" Switched-Mode	90 – 264V	100W	3	5V	8A
13100-123	19" Switched-Mode	90 – 264V	100W	3	5V	8A

Table 2/3

Número de catálogo	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height	Rack Width
13100-122	12V	2.5A	12V	2.5A	3U	8HP
13100-123	15V	2A	15V	2A	3U	8HP

Table 3/3

Número de catálogo	Profundidade	Quantidade por embalagem	Envio rápido
13100-122	171.93mm	1	Não
13100-123	171.93mm	1	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front panel separately.

Output data at mains voltage > 190 VAC, Ta = -25 ... 50 °C.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE