

PSU 19" AC/DC Maxpower 180 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



CARACTERISTICAS

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Efficiency up to 87 %

Integrated active decoupling for redundancy operation

Active Current Share Bus (CSB)

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-153	19" Switched-Mode	90 – 264V	168W	1	24V	7A
13100-151	19" Switched-Mode	90 – 264V	156W	1	12V	13A

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-152	19" Switched-Mode	90 – 264V	165W	1	15V	11A
13100-150	19" Switched-Mode	90 – 264V	150W	1	5V	30A

Table 2/2

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Envio rápido
13100-153	3U	8HP	1	Não
13100-151	3U	8HP	1	Não
13100-152	3U	8HP	1	Não
13100-150	3U	8HP	1	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front panel separately.

Output data for mains voltage > 190 VAC, TA = 0 ... 50 °C.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE