

RackChiller In-Row 45 Height Adapter



The RackChiller In-Row 45 Height Adaptor allows for integration of the cooler into aisle containments of racks higher than 42RU. The top blanking panel assures seamless look while providing best sealing properties of the aisle containment. The kit is available in different heights.

CARACTERISTICAS

Adapts the RackChiller In-Row 45 into aisle containments with racks of 47RU or 52RU

ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Acabamento	Material	Quantidade por embalagem	Rack Height	Largura	Envio rápido
24630-189	Pintura electrostática com Acabamento Texturado	Aço	1	47U	300mm	Não
24630-190	Pintura electrostática com Acabamento Texturado	Aço	1	52U	300mm	Não

DETALHES ADICIONAIS DO PRODUTO

Not to be used in combination with a base plinth

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha

qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE