

Socket Strip, IEC, 3-Phase



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 and C19 outlets with 3 phase input.

CERTIFICATIONS



CARACTERISTICAS

Socket strips with IEC sockets in accordance with IEC 60320

Vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m

Mounting height 1 U

ESPECIFICAÇÕES

Material:	Aluminio; Polyamide
Cor:	Grey; Black; Vermelho
Product Type:	Socket Strip

Table 1/2

Número de catálogo	Tipo de soquete	Socket Quantity	Switched Outlets	Tensão AC	Quantidade por embalagem	Profundidade
60110-285	IEC C13, IEC C19	30	Não	400V	1	44mm

Número de catálogo	Tipo desoquete	SocketQuantity	Switched Outlets	Tensão AC	Quantidade por embalagem	Profundidade
60110-283	IEC C13	18	Não	400V	1	44mm
60110-284	IEC C13, IEC C19	24	Não	400V	1	44mm

Table 2/2				
Número de catálogo	Acabamento	Altura	Length	Envio rápido
60110-285	Anodized	44mm	1753mm	Não
60110-283	Anodized	44mm	947.5mm	Não
60110-284	Anodized	44mm	947.5mm	Não

DETALHES ADICIONAIS DO PRODUTO

Please order bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE