

Varistar CP Air Separation Blanking Cover, Width 800 mm



Filler panel (plain panels) for 800 mm wide cabinets to avoid air recirculation in front to back cooled racks.

CARACTERÍSTICAS

Air separation, covers for 800 mm wide cabinets

Network and server cabinets can be arranged side by side

Gaskets, UL 94 HF-1, -20 °C ... 100° C

Covers solid

Covers prevent unwanted air short-circuits, i.e. unwanted mixing of warm exhaust air with cold inbound air

Only compatible with heavy load crossbar, not compatible with reduction brackets

ESPECIFICAÇÕES

Product Type: Cabinet/Rack Panel

Material: Aço

Table 1/2

Número de catálogo	Rack Height	Altura	Quantidade por embalagem	Cor	Código de cor	Acabamento
21630-141	42U	2000mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado

Número de catálogo	Rack Height	Altura	Quantidade por embalagem	Cor	Código de cor	Acabamento
21630-143	52U	2450mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado
21630-142	47U	2200mm	1	Black Grey	RAL 7021	Pintura electrostática com Acabamento Texturado

Table 2/2

Número de catálogo	Grau de proteção	Tipo	Largura	Envio rápido
21630-141	IP20	Blanking Panel	800mm	Não
21630-143	IP20	Blanking Panel	800mm	Não
21630-142	IP20	Blanking Panel	800mm	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE